



Shure-Lock™ CONTAINER # 21114 LID # 20114 or # 20115

TECHNICAL DATA

Capacity under lid :

With 20114: 1.05 L / 35.67 US oz.
With 20115: 1.03 L / 34.83 US oz.

Wall thickness (approx.) :

Container: 0.73 mm (0.029 in.)
Lid 20114: 0.60 mm (0.026 in.)
Lid 20115: 0.70 mm (0.029 in.)

Thermal range : 0°C (32°F) to 82°C (180°F)

Materials : Container: polypropylene
Lid: polypropylene


Standard colors : clear, natural and white
other colors upon request

Weight (approx.) :


Container: 38.2 g (1.33 oz.)
Lid 20114: 8.0 g (0.26 oz.)
Lid 20115: 9.0 g (0.31 oz.)



(Materials are recyclable or can be recovered for energy)



PRINTING UP TO 6 colors, DRY OFFSET



OPENING AND CLOSING

TO OPEN: Break the Tamper-Evident tab, then remove lid.

TO CLOSE: Snap the lid at break tab area first, then follow all around while releasing air by pressing the center of the lid to burp container. If using a closing device, use proper burping devices.

Fillers, lid, pail denesters and lidding devices are also available in a variety of combinations. Everything can be seen on brochures and video tape. Live demonstration on site can be done on demand.

PACKAGING OF EMPTY CONTAINERS/LIDS

No double stacking, racking recommended.

Approved by:

RECOMMENDATIONS

- IPL recommends to make necessary testing prior to full production.
- Staggered pattern is recommended for greater stability.
- Double faced pallets with close together boards on both sides are recommended for best results.
- To improve stability, release air from container when putting the lid.

Approvals: Virgin materials are approved for food contact and meet FDA (Food and Drug Administration USA) and HPB (Health Protection Branch Canada) regulations.

Advise: Handling conditions vary a lot from customer to customer, tests are recommended throughout the process of denesting, filling, conveying, palletization, warehousing, transportation and utilization by end users, etc. Specifications can be modified without notice. Please contact your IPL representative to confirm these data.

Quality Assurance: . IPL is ISO 9001 certified and quality procedures are documented in our quality system

IPL Plastics Ltd.
20 Boyd Street
P.O. Box 213
Edmundston, NB
Canada E3V-3K8
Tel : (506) 739-9559
Fax : (506) 739-6185
Toll free (Service): 1-800-739-9595

USA
IPL PRODUCTS, LTD.
640 Lincoln Street
Worcester, MA 01605
Tel.:(508)351-6050 Fax.:(508)351-6044
Toll free: 1-800-818-1318

Web Site
www.ipl-packaging.com

